

Sirocco Compressors

Petrol Compressor

The Sirocco Petrol Compressor is designed to deliver clean dry air for installation of optical fibre using the blown fibre technique.

Prysmian Part No. XBFSC00002

Features and Benefits

- > Petrol engine driven rotary vane compressor unit.
- > Pulse free treated compressed air.
- > Honda GX240QX OHV Petrol Engine.
- > Air cooled aftercooler reduces air temp to within 2°C of ambient.
- > 3-stage filtration system provides technically oil-free air.
- > 24vdc outlet socket for supplying the blowing head.



Characteristics

Output	120 l/min
Pressure	10 bar
Noise Level	62dB (A) at 1m
Dimensions (mm)	(h)750 x (w)500 x (d)900
Weight	85kg

Electric Compressors

The Sirocco Electric Compressor is designed to deliver clean dry air for installation of optical fibre using the blown fibre technique.

Prysmian Part Nos. XBFSC00013 (240v/50Hz)
 XBFSC00016 (110v/50Hz)
 XBFSC00042 (120v/60Hz)

Features and Benefits

- > Quiet running.
- > Electrically driven rotary vane compressor unit.
- > Pulse free treated compressed air.
- > Air cooled aftercooler reduces air temp to within 2°C of ambient.
- > 3-stage filtration system provides technically oil-free air.
- > 24vdc outlet socket for supplying the blowing head.



Characteristics

Output	120 l/min
Pressure	10 bar
Noise Level	60dB (A) at 1m
Dimensions (mm)	(h)700 x (w)450 x (d)900
Weight	63kg